



HELUKABEL®

Certificate of compliance with the order 2.1 according to EN 10 204

HELUKABEL® GmbH

Dieselstraße 8 - 12
71282 Hemmingen/Stuttgart
Germany
Phone (0 71 50) 92 09-0
Fax (0 71 50) 8 17 86
www.helukabel.de

Date: 04.10.2016
limited in time: 31.10.2017

**NMHH-J
NMHH-O**

We confirm that the above mentioned emission-free plastic-sheathed cable for fixed installation produced according to DIN VDE 0250 part 215 and tested according to DIN VDE 0473/0481.

- **Temperature range**
 - during installation + 5°C to + 70°C
 - fixed installation - 40°C to + 70°C
- **Nominal voltage** U₀/U 300/500 V

Tests

- Corrosiveness of combustion gases (halogen-free) according to DIN VDE 0482-754-2, DIN EN 60754-2, IEC 60754-2.
- Behaviour in case of fire test according to DIN VDE 0482-332-1-2, DIN EN 60332-1-2, IEC 60332-1-2.
- Low smoke testing according to DIN VDE 0472 part 818.

CE = Product conforms with Low-Voltage Directive 2014/35/EU.

HELUKABEL® GmbH

Verkauf & Lager Berlin
Zum Mühlenfließ 1, 15366 Neuenhagen
Tel. 03342 2397 0 · Fax 03342 80033

Verkauf & Lager Chemnitz
Eichelbergstr. 7, 09212 Limbach-Oberfrohna
Tel. 03722 6086 0 · Fax 03722 6086 420

Verkauf Nord
Viktoriastr. 2, 25524 Itzehoe
Tel. 04821 40394 0 · Fax 04821 40394 29

Verkauf Rhein-Ruhr
Centroallee 261, 46047 Oberhausen
Tel. 0208 882320-0 · Fax 0208 882320-10

Belgien · Brasilien · China · Frankreich · Indien · Indonesien · Italien · Kanada · Malaysia · Mexiko · Niederlande · Österreich · Polen · Portugal · Russland · Singapur · Südafrika · Süd-Korea · Schweden · Schweiz · Thailand · Tschechien · Türkei · UK · USA · Vereinigte Arabische Emirate · Vietnam

Geschäftsführer: Helmut Luksch, Marc Luksch, Andreas Hoppe
Sitz der Gesellschaft: Hemmingen
Amtsgericht Stuttgart HRB 201352
USt-IdNr. DE 146 021 824 · Steuer Nr. 70074/03759
EORI Nummer DE 2623064 · AEO DE AEOF 108137

Baden-Württembergische Bank
Deutsche Bank AG
Kreissparkasse Böblingen
Kreissparkasse Ludwigsburg
Volksbank Ludwigsburg eG

BLZ 600 501 01 KTO 7 832 501 024
BLZ 600 700 70 KTO 987 616 000
BLZ 603 501 30 KTO 8 675 073
BLZ 604 500 50 KTO 30 116 555
BLZ 604 901 50 KTO 45 003 009

SWIFT/BIC SOLADEST600
SWIFT/BIC DEUTDESSXXX
SWIFT/BIC BBKRDE6BXXX
SWIFT/BIC SOLADES1LBG
SWIFT/BIC GENODES1LBG

IBAN DE18 6005 0101 7832 5010 24
IBAN DE21 6007 0070 0987 6160 00
IBAN DE42 6035 0130 0008 6750 73
IBAN DE46 6045 0050 0030 1165 55
IBAN DE39 6049 0150 0045 0030 09