



HELUKABEL®

Certificate of compliance with the order 2.1 according to EN 10 204

HELUKABEL® GmbH

Dieselstraße 8 - 12
71282 Hemmingen/Stuttgart
Germany
Phone (0 71 50) 92 09-0
Fax (0 71 50) 8 17 86
www.helukabel.de

Date: 01.06.2018
limited in time: 30.09.2019

**SY-JZ
SY-OZ**

We confirm that the above mentioned special PVC control cables with steel wire braiding are produced adapted to DIN VDE 0285-525-2-51 / DIN EN 50525-2-51 and tested according to DIN VDE 0473/0481.

- **Temperature range**
flexing - 15°C to + 80°C
fixed installation - 40°C to + 80°C
- **Nominal voltage**
U₀/U 300/500 V

Test

- PVC self-extinguishing and flame retardant according to DIN VDE 0482-332-1-2, DIN EN 60332-1-2, IEC 60332-1-2.

The materials used during manufacturing are cadmium-free, contain no silicone and are free from substances harmful to the wetting properties of lacquers.

CE = Product conforms with Low-Voltage Directive 2014/35/EU.

HELUKABEL® GmbH

Verkauf & Lager Berlin
Zum Mühlenfließ 1, 15366 Neuenhagen
Tel. 03342 2397 0 • Fax 03342 80033

Verkauf & Lager Chemnitz
Eichelbergstr. 7, 09212 Limbach-Oberfrohna
Tel. 03722 6086 0 • Fax 03722 6086 420

Verkauf Nord
Viktoriastr. 2, 25524 Itzehoe
Tel. 04821 40394 0 • Fax 04821 40394 29

Verkauf Rhein-Ruhr
Centraallee 261, 46047 Oberhausen
Tel. 0208 882320-0 • Fax 0208 882320-10

Belgien • Brasilien • Bulgarien • China • Frankreich • Indien • Indonesien • Italien • Kanada • Malaysia • Mexiko • Niederlande • Österreich • Polen • Portugal • Russland • Singapur • Südafrika • Südkorea • Schweden • Schweiz • Thailand • Tschechien • Türkei • USA • Vereinigte Arabische Emirate • Vereinigtes Königreich • Vietnam

Geschäftsführer: Helmut Luksch, Marc Luksch, Andreas Hoppe
Sitz der Gesellschaft: Hemmingen
Amtsgericht Stuttgart HRB 201352
USt-IdNr. DE 146 021 824 • Steuer Nr. 70074/03759
EORI Nummer DE 2623064 • AEO DE AEOF 108137

Baden-Württembergische Bank
Commerzbank AG
Deutsche Bank AG
HSBC Trinkaus & Burkhardt AG
Kreissparkasse Ludwigsburg

SWIFT/BIC SOLADEST600
SWIFT/BIC COBADEFFXXX
SWIFT/BIC DEUTDESSXXX
SWIFT/BIC TUBDDEDDXXX
SWIFT/BIC SOLADES1LBG

IBAN DE18 6005 0101 7832 5010 24
IBAN DE41 6004 0071 0830 7522 00
IBAN DE21 6007 0070 0987 6160 00
IBAN DE77 3003 0880 0500 3320 18
IBAN DE46 6045 0050 0030 1165 55